

SKU: ES-BT BERRCOM INFRARED THERMOMETER



DESCRIPTION:

The Berrcom, non-contact thermometer provides convenience, accuracy and precision when taking a temperature. With the push of a button, Berrcom instantly and accurately takes a person's temperature without the need of any physical contact. Simply point the Berrcom at the patient's forehead, click "Scan" and their temperature instantly will be displayed. Berrcom also comes equipped with three different temperature taking modes; Body, Room and Surface temperature modes.



FEATURES:

- Unit size: 187*120*57 mm(LxWxH)
- Unit weight(without battery): 80g
- Audible alarm if temperature is more than 38°C (100.4°F)
- It can be displayed in either Celsius or Fahrenheit
- Longevity use 100,000 readings
- Eliminates cross contamination
- Accuracy: $\pm 0.3^{\circ}C(0.6^{\circ}F)$
- Response Time: 1 sec
- Suggested Age: Newborn and Up

Ambient temperature10°C ~ 40°C (50°F ~ 104°F)Relative humidity< 85%		
Battery powerDC 3V (2pcs AAA batteries)Display resolution0.1° C (0.1°F)In body mode32°C ~ 43°C (89.6°F ~ 109.4°F)Body mode Precision32.0°C ~ 35.9°C (89.6°F - 96.6°F) +/. 0.3°C (+/.0.6°F)Body mode Precision32.0°C ~ 35.9°C (89.6°F - 102.2°F) +/. 0.3°C (+/.0.6°F)Body mode Precision32.0°C ~ 43.0°C (102.4°F - 109.4°F) +/. 0.3°C (+/.0.6°F)Body mode PrecisionGreen color backlit: ≤37.3°C (99.1°F)normalBacklights color under body modeGreen color backlit: ≤37.3°C (99.1°F)normalBacklights color under body mode0°C ~ 60°C (32°F to 140°F)Surface mode0°C ~ 60°C (32°F to 140°F)Room mode3 cm ~ 5 cm (1.2 in ~ 2 in)Memory3 castsConsumption30mW	Ambient temperature	10°C ~ 40°C (50°F ~ 104°F)
Display resolution 0.1° C (0.1°F) In body mode 32°C ~ 43°C (89.6°F ~ 109.4°F) Body mode Precision 32.0°C ~ 35.9°C (89.6°F - 96.6°F) +/- 0.3°C (+/-0.6°F) Body mode Precision 32.0°C ~ 39.0°C (96.8°F - 102.2°F) +/- 0.2°C (+/-0.4°F) Body mode Precision 39.1°C ~ 43.0°C (102.4°F - 109.4°F) +/- 0.3°C (+/-0.6°F) Backlights color under body mode Green color backlit: ≤37.3°C (99.1°F)normal Mage color backlit: s37.3°C (99.1°F)normal Orange color backlit: s37.3°C (99.1°F)normal Surface mode 0°C ~ 60°C (32°F to 140°F) Room mode 0°C ~ 40°C (32°F to 140°F) Measuring distance 3 cm ~ 5 cm (1.2 in ~ 2 in) Memory 32 sets Consumption 500mW	Relative humidity	≤ 85%
In body mode 32°C ~ 43°C (89.6°F ~ 109.4°F) Body mode Precision 32.0°C ~ 35.9°C (89.6°F - 96.6°F) +/- 0.3°C (+/-0.6°F) Body mode Precision 32.0°C ~ 39.0°C (96.8°F - 102.2°F) +/- 0.3°C (+/-0.6°F) Body mode Precision Green color backlit: ≤37.3°C (99.1°F) - +/- 0.3°C (+/-0.6°F) Backlights color under body mode Green color backlit: ≤37.3°C (99.1°F)normal Backlights color under body mode O'c ~ 60°C (32°F to 104°F) high fever Surface mode 0°C ~ 40°C (32°F to 140°F) Red color backlit: ≥38°C (100.4°F) high fever Sime color backlit: ≥38°C (100.4°F) high fever Red color backlit: ≥38°C (100.4°F) high fever Sime color backlit: ≥38°C (100.4°F) high fever Red color backlit: ≥38°C (100.4°F) high fever Sime color backlit: ≥38°C (100.4°F) high fever Red color backlit: ≥38°C (100.4°F) high fever Sime color backlit: ≥38°C (100.4°F) high fever Red color backlit: ≥38°C (100.4°F) high fever Sime color backlit: ≥38°C (100.4°F) high fever Red color backlit: ≥38°C (100.4°F) high fever Sime color backlit: ≥38°C (100.4°F) high fever Red color backlit: ≥38°C (100.4°F) high fever Sime color backlit: ≥38°C (100.4°F) high fever Red color backlit: ≥38°C (100.4°F) high fever Sime color backlit: ≥38°C (100.4°F) high fever <td>Battery power</td> <td>DC 3V (2pcs AAA batteries)</td>	Battery power	DC 3V (2pcs AAA batteries)
Body mode Precision 32.0°C~35.9°C (89.6°F - 96.6°F) +/- 0.3°C (+/-0.6°F) 36.0°C~39.0°C (96.8°F - 102.2°F) +/- 0.3°C (+/-0.4°F) 39.1°C~43.0°C (102.4°F - 109.4°F) +/- 0.3°C (+/-0.6°F) Backlights color under body mode Green color backlit ≤37.3°C (99.1°F)normal Backlights color under body mode Orange color backlit: ≤37.3°C (99.1°F)normal Variage color backlit: ≤37.3°C (99.1°F)normal Orange color backlit: ≤37.3°C (99.3°F~100.2°F)low fever Red color backlit: ≤38°C (100.4°F) high fever Red color backlit: ≥38°C (100.4°F) high fever Surface mode 0°C ~ 60°C (32°F to 140°F) Neasuring distance 3 cm ~ 5 cm (1.2 in ~ 2 in) Memory 32 sets Consumption ≤ 300mW	Display resolution	0.1° C (0.1°F)
Body mode Precision 36.0°C~39.0°C (96.8°F - 102.2°F) +/- 0.2°C(+/-0.4°F) 39.1°C~43.0°C (102.4°F - 109.4°F) +/- 0.3°C(+/-0.6°F) Green color backlit: ≤37.3°C (99.1°F)normal Backlights color under body mode Green color backlit: ≤37.3°C (99.1°F)normal Orange color backlit: ≤37.3°C (99.1°F)normal Surface mode O°C ~ 60°C (32°F to 140°F)- Red color backlit: ≥38°C (100.4°F) high fever Surface mode 0°C ~ 60°C (32°F to 140°F) 0°C ~ 40°C (32°F to 104°F) Measuring distance 3 cm ~ 5 cm (1.2 in ~ 2 in) 32 sets Consumption ≤ 300mW Surface mode	In body mode	32°C ~ 43°C (89.6°F ~109.4°F)
36.0°C~39.0°C (96.8°F - 102.2°F) +/- 0.2°C(+/-0.4°F) 39.1°C~43.0°C (102.4°F - 109.4°F) +/- 0.3°C(+/-0.6°F) 39.1°C~43.0°C (102.4°F - 109.4°F) +/- 0.3°C(+/-0.6°F) Backlights color under body mode Green color backlit: ≤37.3°C (99.1°F)normal Orange color backlit: ≤37.3°C (99.1°F)normal Orange color backlit: ≤37.3°C (99.3°F~100.2°F)low fever Red color backlit: ≥38°C (100.4°F) high fever Red color backlit: ≥38°C (100.4°F) high fever Surface mode 0°C ~ 60°C (32°F to 140°F) Room mode 0°C ~ 40°C (32°F to 104°F) Measuring distance 3 cm ~ 5 cm (1.2 in ~ 2 in) Memory 32 sets Consumption ≤ 300mW	Body mode Precision	32.0°C~35.9°C (89.6°F - 96.6°F) +/- 0.3°C (+/-0.6°F)
Backlights color under body mode Green color backlit: ≤37.3°C (99.1°F)normal Orange color backlit: ≤37.3°C (99.1°F)normal Orange color backlit: ≤37.3°C (99.1°F)normal Surface mode Orange color backlit: 37.4°C~37.9°C (99.3°F~100.2°F)low fever Red color backlit: ≥38°C (100.4°F) high fever Red color backlit: ≥38°C (100.4°F) high fever Surface mode 0°C ~ 60°C (32°F to 140°F) Room mode 0°C ~ 40°C (32°F to 104°F) Measuring distance 3 cm ~ 5 cm (1.2 in ~ 2 in) Memory 32 sets Consumption ≤ 300mW		36.0°C~39.0°C (96.8°F - 102.2°F) +/- 0.2°C(+/-0.4°F)
Backlights color under body mode Orange color backlit: 37. 4°C~37.9°C (99.3°F~100.2°F)low fever Red color backlit: ≥38°C (100.4°F) high fever Surface mode 0°C ~ 60°C (32°F to 140°F) Room mode 0°C ~ 40°C (32°F to 104°F) Measuring distance 3 cm ~ 5 cm (1.2 in ~ 2 in) Memory 32 sets Consumption ≤ 300mW		39.1°C~43.0°C (102.4°F - 109.4°F) +/- 0.3°C(+/-0.6°F)
mode Orange color backlit: 37. 4°C~37.9°C (99.3°F~100.2°F)low fever Red color backlit: ≥38°C (100.4°F) high fever Surface mode 0°C ~ 60°C (32°F to 140°F) Room mode 0°C ~ 40°C (32°F to 104°F) Measuring distance 3 cm ~ 5 cm (1.2 in ~ 2 in) Memory 32 sets Consumption ≤ 300mW		Green color backlit: ≤37.3°C (99.1°F)normal
Surface mode 0°C ~ 60°C (32°F to 140°F) Room mode 0°C ~ 40°C (32°F to 104°F) Measuring distance 3 cm ~ 5 cm (1.2 in ~ 2 in) Memory 32 sets Consumption ≤ 300mW		Orange color backlit: 37. 4°C~37 .9°C (99.3°F~100.2°F)low fever
Room mode 0°C ~ 40°C (32°F to 104°F) Measuring distance 3 cm ~ 5 cm (1.2 in ~ 2 in) Memory 32 sets Consumption ≤ 300mW		Red color backlit: ≥38°C (100.4°F) high fever
Measuring distance 3 cm ~ 5 cm (1.2 in ~ 2 in) Memory 32 sets Consumption ≤ 300mW	Surface mode	0°C ~ 60°C (32°F to 140°F)
Memory 32 sets Consumption ≤ 300mW	Room mode	0°C ~ 40°C (32°F to 104°F)
Consumption ≤ 300mW	Measuring distance	3 cm ~ 5 cm (1.2 in ~ 2 in)
	Memory	32 sets
Automatic power off 30secs	Consumption	≤ 300mW
	Automatic power-off	30secs